



50X125HSSBUS, 1/2" x 1-1/4" Hex Bolt, Stainless Steel

By Burndy
Catalog # [50X125HSSBUS](#)

Stainless Steel Hex Head Bolt, 1-1/4 IN Stud, 1/2 IN-#13 Thread Size

Features

- Stainless Steel hardware is manufactured from 18-8 non-magnetic material
- Nut surfaces and bolt heads have American National Coarse Series, Class #2 fit

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Bolt - Hex
----------------	------------

Dimensions

Package Height	0.000 in
Dimension - Bolt Size fraction	1/2
Length	1.25 in
Dimension - B Length fraction	1-1/4 in
Package Weight	0.000 lb.
Package Length	0.000 in



Package Width	0.000 in
Dimension - B Length inch	1.25 in
Height	0.364 in
Width	0.5 in
Dimension - Thread Size	1/2-13
Dimension - Threads per inch	13
Dimension - Bolt Size inch	0.5 in
Dimensions	1.25 in x 0.5 in x 0.364 in

Force Related

Installation Torque	480 LBS/in
Recommended in-lb	

General

UPC	781810339138
Material	Stainless Steel
UPC 12 Digit	781810339138
UPC 14 Digit GTIN	00781810339138

Logistics

Minimum Pack Quantity	1
Pallet Quantity	46400
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)