



50X250HSSBBOX, 1/2" x 250" Hex Bolt, Stainless Steel

By Burndy
Catalog # [50X250HSSBBOX](#)

Stainless Steel Hexagonal Head Bolt, 2.50 IN L, 1/2 IN-13 Thread Size

Features

- Stainless Steel hardware is manufactured from 18-8 non-magnetic material
- Nut surfaces and bolt heads have American National Coarse Series, Class #2 fit

Application

For Use On Outdoor Connector Applications

Specifications

Certification - cULus	No
EU RoHS Indicator	Yes
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No
Buy America(n) Qualified	Contact Manufacturer

Configuration

Connector Type	Bolt - Hex
----------------	------------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length fraction	2-1/2 in
Package Weight	0.000 lb.
Dimension - B Length inch	2.5 in



Package Height	0.000 in
Length	2.5 in
Dimension - Bolt Size fraction	1/2
Dimension - Bolt Size inch	0.5 in
Width	0.5 in
Height	0.364 in
Dimension - Thread Size	1/2-13
Dimension - Threads per inch	13
Dimensions	2.5 in x 0.5 in x 0.364 in

Force Related

Installation Torque	480 LBS/in
Recommended in-lb	

General

Sub Brand	HARDWARE BOLT
Type	HSSB,Hexagonal Bolts
UPC 12 Digit	781810361535
UPC 14 Digit GTIN	00781810361535
Material	Stainless Steel
UPC	781810361535

Logistics

Minimum Pack Quantity	1
Carton Quantity	1000
Pallet Quantity	58000

Product Assets

[Catalog \[English\]](#)