



50X250OSBBOX, 1/2" x 2-1/2" Oval Shank Bolt



By Burndy
Catalog # [50X250OSBBOX](#)

1/2 x 2.50 Oval Shank Bolt

Features

- Prevents Rotation
- Increased Stability
- Reduces wear and tear on the hole and bolt
- Improved load distribution and specified application fit

Specifications

Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No

Configuration

Connector Type	Bolt - Oval Shank
----------------	-------------------

Dimensions

Dimension - Bolt Size fraction	1/2
Length	2.5 in
Dimension - B Length fraction	2-1/2 in
Dimension - B Length inch	2.5 in
Height	0.364 in

Width	0.5 in
Dimension - Thread Size	1/2-13
Dimension - Threads per inch	13
Dimension - Bolt Size inch	0.5 in
Dimensions	2.5 in x 0.5 in x 0.364 in

Force Related

Installation Torque Recommended in-lb	480 LBS/in
---------------------------------------	------------

General

UPC	781810362044
Material	SILICON BRONZE
UPC 12 Digit	781810362044
UPC 14 Digit GTIN	00781810362044

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Catalog \[English\]](#)