



50X300HSSBBOX, 1/2" x 3" Hex Bolt, Stainless Steel

By Burndy
Catalog # 50X300HSSBBOX

Stainless Steel Bolt, 3 in L, Thread Size: 1/2-13 in



Features

- Stainless Steel hardware is manufactured from 18-8 non-magnetic material
- Nut surfaces and bolt heads have American National Coarse Series, Class #2 fit

Application

For Use On Outdoor Connector Applications

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Bolt - Hex
----------------	------------

Dimensions

Package Height	0.000 in
Dimension - Bolt Size fraction	1/2
Length	3 in
Dimension - B Length fraction	3 in
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	3 in
Height	0.364 in
Width	0.5 in
Dimension - Thread Size	1/2-13
Dimension - Threads per inch	13
Dimension - Bolt Size inch	0.5 in
Dimensions	3 in x 0.5 in x 0.364 in

Force Related

Installation Torque	480 LBS/in
Recommended in-lb	

General

Sub Brand	STAINLESS STEEL HARDWARE
UPC	781810361153
Type	Bolt
Material	Stainless Steel
UPC 12 Digit	78181036115
UPC 14 Digit GTIN	00781810361153

Logistics

Minimum Pack Quantity	1
Pallet Quantity	11100
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)