



50X500HEBBOX, 1/2" x 5" Hex Bolt, Silicon Bronze

By Burndy
Catalog # 50X500HEBBOX

Silicon Bronze Hexagonal Head Bolt, 5.00 IN L, 1/2 IN-13 Thread Size

Features

- DURIMUM™ silicon bronze hardware combines high strength and corrosion resistance
- Silicon bronze per ASTM B99

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Bolt - Hex
----------------	------------

Dimensions

Package Height	0.000 in
Dimension - Bolt Size fraction	1/2
Length	5 in
Dimension - B Length fraction	5 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	5 in



Height	0.364 in
Width	0.5 in
Dimension - Thread Size	1/2-13
Dimension - Threads per inch	13
Dimension - Bolt Size inch	0.5 in
Dimension - Length Overall	5 in
inch	
Dimensions	5 in x 0.5 in x 0.364 in

Force Related

Installation Torque	480 LBS/in
Recommended in-lb	

General

Trade Name	DURIMUM™
UPC	781810011706
Material	Silicon Bronze
UPC 12 Digit	781810011706
UPC 14 Digit GTIN	00781810011706

Logistics

Minimum Pack Quantity	1
Pallet Quantity	4900
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)