



62X175HGSB, 5/8" x 1-3/4" Hex Bolt,
Galvanized Steel

By Burndy
Catalog # [62X175HGSB](#)

5/8 x 1.75 Galvanized Steel Hex Bolt



Features

- Galvanized steel hardware (bolts, nuts, flatwashers and internal tooth lockwashers) are manufactured per ASTM307 Grade A
- Nut surfaces and bolt heads have American Standard dimensions
- Galvanizing is per ASTM A153

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	NC
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Dimensions

Width	0.62 in
-------	---------

Dimension - Bolt Size fraction	5/8
Length	1.75 in
Dimension - Thread Size	5/8-11
Dimension - Threads per inch	11
Dimension - B Length fraction	1-3/4 in
Dimension - Bolt Size inch	0.625 in
Dimension - Length Overall	1.75 in
inch	
Dimension - B Length inch	1.75 in

General

UPC	781810435397
Material	Galvanized Steel

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)