



723003-1T, Tap Shear Bolt Connector, 2-Hole Pad

By Burndy
Catalog # [723003-1T](#)



Conductor Range: 1/0 - 4/0 AAC (.368" - .522") Tin Plated

Features

- Easy to remove and re-use without damaging the conductor
- Available in NEMA standard 2- or 4-hole patterns
- Industry-proven wedge technology for quick and easy installation without the need for special tools
- Easily adaptable to standard hotstick tools
- High-conductivity grit corrosion inhibitor is factory applied for ease of installation and longevity while the connector is in service
- Meets or exceeds the current carrying capacity of the conductors being connected
- Remains permanently locked through fault current or power surges
- May be used in non-corrosive environments to connect copper conductors

- Excellent option for emergency restoration applications where outside crews might not have shoot-on or compression tooling

General

Catalog Number 723003-1T
UPC 621945674677

Conductor Related

Conductor Range 1/0-4/0 AAC

Product Assets

[Installation Manuals - Tap Connector Installation Instructions](#)
[Specifications - 7230031T](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BRDY-7230031T-SPEC-EN | REV 7/2025