



ACC-ECTB1214, Horiz 180 Degree Edge Clip w/Nylon 12 Tie, 14"

By Wiley
Catalog # [ACC-ECTB1214](#)

Wiley Edge Clip with Cable Tie



Features

- Route cable bundles without the need for mounting holes or additional hardware
- Installs in a vertical/parallel (90°) or horizontal/perpendicular (180°) orientation
- Steel lances securely anchor clips to module frames or purlins
- Offered in various nylon types with 50 lb tensile strength
- UV resistant, high impact heat stabilized Nylon 6/6
- UV resistant Nylon 12 which provides excellent UV, chemical and moisture resistance

Application

For routing cable bundles without requiring mounting holes or additional hardware, Available in Nylon 6/6 or Nylon 12 for either horizontal/perpendicular (90°) or vertical/ parallel (180°) styles;50 lb tensile strength, Steel lances securely anchor clips to module frames / purlins, 3 standard cable tie lengths (8", 11", 14") encompass maximum bundle diameters of 1.95" to 3.94";Custom lengths available

Specifications

Industry Standard(s)	UL62275 Recognized
Certified Listed	UL62275 Recognized
Certification - cULus	No
Certification - CSA Approved	No

Dimensions

Height	0.5 in
Width	0.5 in
Package Height	0.000 in
Length	14 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Bundle Diameter Max inch	3.94 in
Dimensions	14 in x 0.5 in x 0.5 in

Force Related

Tensile Strength	50 lb.
------------------	--------

General

UPC	621945554429
Installation Type	Horizontal (180 Deg.) perpendicular installation
Material	Nylon 12

Logistics

Pallet Quantity	1
Carton Quantity	1000

Product Assets

[Catalog \[English\]](#)