ACC-ECTB68, Horizontal 180 Degree Edge Clip with Nylon6/6 Cable Tie, 8″

By Burndy
Catalog # ACC-ECTB68

Wiley Edge Clip with Cable Tie, Horizontal (180 Deg.) perpendicular installation.

Application

- For routing cable bundles without requiring mounting holes or additional hardware, Available in Nylon 6/6 or Nylon 12 for either horizontal/perpendicular (90°) or vertical/ parallel (180°) styles
- 50 lb tensile strength, Steel lances securely anchor clips to module frames / purlins, 3 standard cable tie lengths (8”, 11”, 14”) encompass maximum bundle diameters of 1.95” to 3.94”
- Custom lengths available

General

Catalog Number	ACC-ECTB68
Installation Type	Horizontal (180 Deg.) perpendicular installation
Material	Nylon 6/6
Tensile Strength	50 lb.
UPC	621945554375

Dimensions

Dimension - Bundle Diameter Max inch	1.95 in
Length	8 in

Certifications And Compliance

Certification - CSA Approved	No
Certification - cULus	No
Certified Listed	UL62275 Recognized
Industry Standard(s)	UL62275 Recognized

Logistics

Carton Quantity	1000

Product Assets

Catalogs - BURNDY Master Catalog - Section E4 - Wiley Grounding
Catalogs - Wiley Wire Management Guide
Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
Catalogs - BURNDY Master Catalog - Section G - Wire Management
Certifications - UL Certificate of Compliance UL 62275
Interactive Catalog - BURNDY Full-Line Digital Catalog
Sales Drawings - 50100741
Specifications - ACCECTB68 Specification Sheet English
Specifications - ACC-ECTB68 Specification Sheet French
Video - ACC-ECT
Video - Wiley ACC-ECT Edge Clip / Cable Tie Combo
Video - Wiley ACC-ECT Edge Clip / Cable Tie Combo

©2025 Hubbell Incorporated. All rights reserved