



AYPO3/0, Compression Pin Adapter, 3/0 AWG, AL9CU

By Burndy
Catalog # [AYPO3/0](#)

3/0 AWG, Aluminum Termination, Offset Pin, .37" Pin Dia, 1.22" Pin Length

Features

- All-aluminum electro-tin plated design eliminates possible bi-metallic corrosion
- Provides the shortest connector length design possible permitting easy installation in equipment with limited working space
- Solid electro-tin plated aluminum plug
- Proper electrical connection made easily and eliminates the "how tight is tight" issue
- Solid plug has equivalent cross-sectional area as current carrying equivalent copper wire permitting use of larger aluminum wire to connect equipment
- Offset plug design available in sizes 2/0 through 750 kcmil providing flexibility and maximizing the use of limited space while eliminating interference between conductors and equipment
- Electro-tin plating resists corrosion
- Factory pre-filled with PENETROX oxide inhibiting compound with conductive metallic particles to penetrate aluminum oxide between strands and forms an air-tight connection
- EPDM rubber covers supplied with each connector and rated for 600V eliminating taping
- Only 5 die sets are required to install the complete line from #6 to 750 kcmil reducing inventory requirements
- Supplied in plastic convenience pack so cover and connector are kept together and free of foreign material until opened
- Connectors are clearly marked with catalog number, wire size, along with a color-coded die index providing clear, easy to use information

Application

Wire Termination

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Yes
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes



Certification - CSA Approved Yes

Conductor

Conductor - Material	ALUMINUM / COPPER
Wire Size	3/0 AWG
Conductor - AL Str Size	3/0 AWG
Conductor - AL Str Size Range	3/0 AWG
Conductor - Copper Str Size	3/0 AWG
Conductor - Copper Flex I Size Range	2/0 AWG
Conductor - Copper DLO Size Range	2/0 AWG
Conductor - Copper Str Compact Size	3/0 AWG
Conductor - Copper DLO Size	2/0 AWG
Conductor Size	3/0 AWG
Conductor - Copper Solid Size	3/0 AWG
Conductor - Copper Solid Size Range	3/0 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	3/0 AWG
Conductor - Copper Flex I Size	3/0 AWG

Configuration

Physical Attribute - Number of Crimps Required	2
Connector Type	OFFSET PIN

Current

Voltage Rating	35 kV
Voltage - Maximum	35000 V

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - P inch	1.22 in
Dimension - L Length Overall mm	71 mm
Width	0.86 in
Dimension - A Outside	.85 in
Diameter inch	
Dimension - Strip Length inch	1-1/8 in

Length	2.8 in
Equivalent Pin Size	1/0 AWG
Dimension - B Length fraction	1-1/8 in
Dimension - B Length inch	1.11 in
Dimension - B Outside	0.37 in
Diameter inch	
Height	0.86 in
Dimension - Length Overall inch	2.80 in
Dimensions	2.8 in x 0.86 in x 0.86 in

General

Insulation Type	Rubber
Trade Name	HYPLUG™
Die Index	298
Insulation	Y
Terminal Type	Pin
Plated	Y
Color Code	White
Pin Type	Solid

Sub Brand	HYPLUG
UPC	781810738337
Type	Aluminum Pin Adapters
Material	Aluminum
Plating Type	Tin
Finish Type	Tin-Plated
UPC 12 Digit	781810738337
UPC 14 Digit GTIN	00781810738337

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2960
Carton Quantity	10

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)

