



B21D20D25CG1 Flexible Copper Braid, U-Shape

By Burndy
Catalog # B21D20D25CG1

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Current

Rating - Indoor Amperage	304
Rating - Outdoor Amperage	364

Dimensions

Package Height	0.000 in
Length	9.41 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	514 mm
mm	
Height	2 in
Width	3.23 in
Dimension - Length Overall	20.25 in
inch	
Dimensions	9.41 in x 3.23 in x 2 in

General

Plated	Y
Material - Ferrules	Y
Physical Attribute - Number of	2
Braids	
UPC	781810460382
Material	Copper
UPC 12 Digit	781810460382
UPC 14 Digit GTIN	00781810460382

Logistics

Minimum Pack Quantity	1
Pallet Quantity	864
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)