



# B21E12G22 Flexible Copper Braid

By Burndy  
Catalog # B21E12G22

Flexible Copper Braid



## Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

## Specifications

|                               |     |
|-------------------------------|-----|
| Certification - ETL           | No  |
| Certification - UL Recognized | No  |
| Standards - RoHS Compliance   | EX  |
| Status                        |     |
| Certification - cULus         | No  |
| UL Listed                     | Yes |
| Certification - CSA Approved  | Yes |

## Configuration

|                |       |
|----------------|-------|
| Connector Type | Braid |
|----------------|-------|

## Current

|                           |     |
|---------------------------|-----|
| Rating - Outdoor Amperage | 400 |
|---------------------------|-----|

## Dimensions

|                              |                        |
|------------------------------|------------------------|
| Package Height               | 0.000 in               |
| Length                       | 12 in                  |
| Package Weight               | 0.000 lb.              |
| Package Length               | 0.000 in               |
| Package Width                | 0.000 in               |
| Dimension - L Length Overall | 305 mm                 |
| mm                           |                        |
| Height                       | 0.25 in                |
| Width                        | 3 in                   |
| Dimension - Length Overall   | 12.00 in               |
| inch                         |                        |
| Dimensions                   | 12 in x 3 in x 0.25 in |

## General

|                                |                |
|--------------------------------|----------------|
| Plated                         | Y              |
| Material - Ferrules            | Y              |
| Physical Attribute - Number of | 2              |
| Braids                         |                |
| UPC                            | 781810327371   |
| Material                       | Copper         |
| UPC 12 Digit                   | 781810327371   |
| UPC 14 Digit GTIN              | 00781810327371 |

## Logistics

|                       |     |
|-----------------------|-----|
| Minimum Pack Quantity | 1   |
| Pallet Quantity       | 672 |
| Carton Quantity       | 4   |

## Product Assets

[Catalog \[English\]](#)