



B21E4D75G29 Flexible Copper Braid

By Burndy
Catalog # [B21E4D75G29](#)

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Dimensions

Length	4.75 in
Dimension - L Length Overall	121 mm
mm	
Dimension - Length Overall	4.75 in
inch	

General

UPC	621945435759
Material	Copper
UPC 12 Digit	621945435759
UPC 14 Digit GTIN	00621945435759

Logistics

Minimum Pack Quantity	50
Pallet Quantity	12000
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)