



# B21E964NTN Flexible Copper Braid, Tin Plated Ferrules

By Burndy  
Catalog # [B21E964NTN](#)

Flexible Copper Braid



## Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:

[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

## Specifications

Standards - RoHS Compliance    CM  
Status

## Configuration

Connector Type                      Braid

## Current

Rating - Outdoor Amperage        530

## Dimensions

Length                                      96 in  
Dimension - L Length Overall       2438 mm  
mm  
Dimension - Length Overall        96.00 in  
inch

## General

Plated                                        Y  
Material - Ferrules                      Y  
Physical Attribute - Number of      2  
Braids  
UPC                                            781810478875  
Material                                      Copper  
UPC 12 Digit                                781810478875  
UPC 14 Digit GTIN                        00781810478875

## Logistics

Minimum Pack Quantity                5

## Product Assets

[Catalog \[English\]](#)