



# B22E124N Flexible Copper Braid

By Burndy  
Catalog # B22E124N

Flexible Copper Braid



## Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

## Specifications

|                                    |    |
|------------------------------------|----|
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Standards - RoHS Compliance Status | EX |
| Certification - cULus              | No |
| UL Listed                          | No |
| Certification - CSA Approved       | No |

## Configuration

|                |       |
|----------------|-------|
| Connector Type | Braid |
|----------------|-------|

## Current

|                           |       |
|---------------------------|-------|
| Rating - Outdoor Amperage | 800 A |
|---------------------------|-------|

## Dimensions

|                              |           |
|------------------------------|-----------|
| Package Height               | 0.000 in  |
| Length                       | 12 in     |
| Package Weight               | 0.000 lb. |
| Package Length               | 0.000 in  |
| Package Width                | 0.000 in  |
| Dimension - L Length Overall | 305 mm    |
| mm                           |           |
| Dimension - Hole Size inch   | 0.56 in   |
| Dimension - Length Overall   | 12.00 in  |
| inch                         |           |

## General

|                                       |                |
|---------------------------------------|----------------|
| Plated                                | N              |
| Material - Ferrules                   | Y              |
| Physical Attribute - Number of Braids | 4              |
| UPC                                   | 781810511183   |
| Material                              | Copper         |
| UPC 12 Digit                          | 781810511183   |
| UPC 14 Digit GTIN                     | 00781810511183 |

## Logistics

|                       |     |
|-----------------------|-----|
| Minimum Pack Quantity | 1   |
| Pallet Quantity       | 360 |
| Carton Quantity       | 4   |

## Product Assets

[Catalog \[English\]](#)