



# B22E724NTN Flexible Copper Braid, Tin Plated Ferrules

By Burndy  
Catalog # B22E724NTN

Flexible Copper Braid



## Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](http://www.hubbell.com/config/BRAID) for our Braid Configurator Tool:

## Specifications

|                               |    |
|-------------------------------|----|
| Certification - ETL           | No |
| Certification - UL Recognized | No |
| Standards - RoHS Compliance   | EX |
| Status                        |    |
| Certification - cULus         | No |
| UL Listed                     | No |
| Certification - CSA Approved  | No |

## Configuration

|                |       |
|----------------|-------|
| Connector Type | Braid |
|----------------|-------|

## Dimensions

|                              |         |
|------------------------------|---------|
| Length                       | 72 in   |
| Thickness                    | 0.38 in |
| Dimension - L Length Overall | 1829 mm |
| mm                           |         |
| Dimension - Hole Size inch   | 0.56 in |
| Dimension - Length Overall   | 72 in   |
| inch                         |         |

## General

|                                |                    |
|--------------------------------|--------------------|
| Plated                         | Y                  |
| Material - Ferrules            | Y                  |
| Physical Attribute - Number of | 4                  |
| Braids                         |                    |
| UPC                            | 781810281185       |
| Material                       | Copper             |
| Plating Type                   | Electro tin plated |
| UPC 12 Digit                   | 781810281185       |
| UPC 14 Digit GTIN              | 00781810281185     |

## Logistics

|                       |     |
|-----------------------|-----|
| Minimum Pack Quantity | 1   |
| Pallet Quantity       | 360 |
| Carton Quantity       | 4   |

## Product Assets

[Catalog \[English\]](#)