



B22F284N Flexible Copper Braid

By Burndy
Catalog # [B22F284N](#)

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance EX
Status

Configuration

Connector Type Braid

Current

Amperage Rating 1100 A

Dimensions

Dimension - Pad Width inch	3.00 in
Package Height	0.000 in
Length	28 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	711 mm
Dimension - D inch	3.06 in
Dimension - N inch	0.62 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	28.00 in

General

UPC	781810308448
Material	Copper
UPC 12 Digit	781810308448
UPC 14 Digit GTIN	00781810308448

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)