



# B22G144N Flexible Copper Braid

By Burndy  
Catalog # B22G144N

Flexible Copper Braid



## Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

## Specifications

|                               |    |
|-------------------------------|----|
| Certification - ETL           | No |
| Certification - UL Recognized | No |
| Standards - RoHS Compliance   | EX |
| Status                        |    |
| Certification - cULus         | No |
| UL Listed                     | No |
| Certification - CSA Approved  | No |

## Configuration

|                |       |
|----------------|-------|
| Connector Type | Braid |
|----------------|-------|

## Current

|                           |        |
|---------------------------|--------|
| Rating - Outdoor Amperage | 1300 A |
|---------------------------|--------|

## Dimensions

|                              |         |
|------------------------------|---------|
| Length                       | 14 in   |
| Dimension - L Length Overall | 356 mm  |
| Dimension - Hole Size        | 0.56 in |
| Dimension - Length Overall   | 14 in   |

## General

|                                       |                |
|---------------------------------------|----------------|
| Plated                                | Y              |
| Material - Ferrules                   | Y              |
| Physical Attribute - Number of Braids | 4              |
| UPC                                   | 781810242971   |
| Material                              | Copper         |
| UPC 12 Digit                          | 781810242971   |
| UPC 14 Digit GTIN                     | 00781810242971 |

## Logistics

|                       |      |
|-----------------------|------|
| Minimum Pack Quantity | 1    |
| Pallet Quantity       | 2250 |
| Carton Quantity       | 25   |

## Product Assets

[Catalog \[English\]](#)