



B22G204NTN Flexible Copper Braid

By Burndy
Catalog # B22G204NTN

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Dimensions

Length	20 in
Dimension - Width mm	76 mm
Dimension - Width inch	3
Dimension - L Length Overall mm	508
Height	0.56 in
Width	3 in
Dimension - Length Overall inch	20
Dimensions	20 in x 3 in x 0.56 in

General

Material - Ferrules	Copper
UPC	781810657423
Material	Copper
UPC 12 Digit	781810657423
UPC 14 Digit GTIN	00781810657423

Logistics

Minimum Pack Quantity	1
Pallet Quantity	150
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)