



B22G26G31W Flexible Copper Braid

By Burndy
Catalog # [B22G26G31W](#)

Tin Plated Ferrules.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	B22G26G31W
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
UPC	781810210796

UPC 14 Digit GTIN 00781810210796

Dimensions

Length 26 in

Electrical Ratings

Amperage Rating 1200 A
Rating - Outdoor Amperage 1200

Certifications And Compliance

Standards - RoHS Compliance EX
Status
UL Listed No

Logistics

Carton Quantity 1
Minimum Pack Quantity 1

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 10105858](#)
[Specifications - B22G26G31W](#)



A Hubbell brand