



B22G364NTN Flexible Copper Braid

By Burndy
Catalog # [B22G364NTN](#)

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Current

Amperage Rating	1300 A
-----------------	--------

Dimensions

Length	36 in
Dimension - Width mm	76 mm
Dimension - Width inch	3
Dimension - L Length Overall mm	914
Height	0.56 in
Width	3 in
Dimension - Length Overall inch	36
Dimensions	36 in x 3 in x 0.56 in

General

Material - Ferrules	Copper
Physical Attribute - Number of Braids	4
UPC	781810654620
Material	Copper
UPC 12 Digit	781810654620
UPC 14 Digit GTIN	00781810654620

Logistics

Minimum Pack Quantity	1
Pallet Quantity	900
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)