



B22G784NTN Flexible tinned copper braid 78.00"x3.00"x0.56"

By Burndy
Catalog # B22G784NTN

Flexible tinned copper braid 78.00"x3.00"x0.56"



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Current

Amperage Rating	1300 A
-----------------	--------

Dimensions

Length	78 in
Dimension - Width mm	76 mm
Dimension - Width inch	3.00
Dimension - L Length Overall mm	1981
Height	0.56 in
Width	3 in
Dimension - Length Overall inch	78.00
Dimensions	78 in x 3 in x 0.56 in

General

Material - Ferrules	Tin Plated Copper
Physical Attribute - Number of Braids	4
UPC	781810657430
Material	Copper
UPC 12 Digit	781810657430
UPC 14 Digit GTIN	00781810657430

Logistics

Minimum Pack Quantity	1
Pallet Quantity	60
Carton Quantity	2

Product Assets

[Catalog \[English\]](#)