



B23G184NTN Flexible Copper Braid

By Burndy
Catalog # B23G184NTN

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](http://www.hubbell.com/config/BRAID) for our Braid Configurator Tool:

Specifications

Standards - RoHS Compliance	UI
Status	
Certification - CSA Approved	No

Configuration

Connector Type	Braid
Dimensions	
Length	18 in
Dimension - Width inch	3 in
Height	0.66 in
Width	3 in
Dimension - Length Overall inch	18 in
Dimensions	18 in x 3 in x 0.66 in

General

Material - Ferrules	Tin Plated Copper
UPC	621945270893
Material	Copper
UPC 12 Digit	621945270893
UPC 14 Digit GTIN	00621945270893

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalog \[English\]](#)