



B243, Horizontal Cable Tap to Horizontal Cable Run, 4/0 AWG (Run), 2/0 AWG (Tap)

By Burndy
Catalog # [B243](#)

Horizontal Cable Tap to Horizontal Cable Run Mold

Application

For Joining Horizontal Cable Tap To A Horizontal Run Cable

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
EU RoHS Indicator	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	4/0 AWG
Conductor - Copper Str Run	4/0 AWG
Conductor Type	- CU C Str-Run - CU C Str-Tap
Conductor - Copper Str Tap Range	2/0 AWG

Conductor - Copper Str Tap 2/0 AWG

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

Sub Brand	BURNDYWELD
UPC	781810378649
UPC 12 Digit	781810378649
UPC 14 Digit GTIN	00781810378649

Logistics

Pallet Quantity	480
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)