



B246, Horizontal Cable Tap to Horizontal Cable Run, 4/0 AWG (Run), 2 AWG (Tap)

By Burndy
Catalog # [B246](#)



Mold, Horizontal Cable Tap to Horizontal Cable Run, 4/0 AWG (Run), 2 AWG (Tap), 90 Weld Metal.

Application

For Joining Horizontal Cable Tap To A Horizontal Run Cable

General

Catalog Number	B246
EU RoHS Indicator	Yes
Sub Brand	BURNDYWELD
Trade Name	BURNDYWeld®
UPC	781810378700
UPC 14 Digit GTIN	00781810378700

Conductor Related

Conductor - Copper Str Run	4/0 AWG
Conductor - Copper Str Run Range	4/0 AWG
Conductor - Copper Str Tap	2 AWG
Conductor - Copper Str Tap Range	2 AWG
Conductor Type	• CU C Str-Run • CU C Str-Tap

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	1
Pallet Quantity	480

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_BCC-2_LineArt](#)
- [Sales Drawings - 10044340](#)
- [Specifications - B246 Specification Sheet French](#)
- [Specifications - B246 Specification Sheet English](#)



A Hubbell brand