



B24B100L18UTNNOVG1 Flexible Copper Braid

By Burndy
Catalog # [B24B100L18UTNNOVG1](#)

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Dimensions

Package Height	0.000 in
Length	18 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	457 mm
Weight	8.064 lb.
Dimension - Length Overall	18 inch

General

Plated	y
Material - Ferrules	Y
Physical Attribute - Number of Braids	8
UPC	621945456846
Material	Copper
UPC 14 Digit GTIN	00621945456846

Logistics

Minimum Pack Quantity	1
Pallet Quantity	480
Carton Quantity	5

Product Assets

[Catalog \[English\]](#)