



B24G844NTN Flexible Copper Braid

By Burndy
Catalog # [B24G844NTN](#)

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Current

Rating - Outdoor Amperage	2000
---------------------------	------

Dimensions

Dimension - Pad Width inch	3
Length	84 in
Dimension - L Length Overall mm	2134 mm
Height	1 in
Width	3 in
Dimension - D inch	3
Dimension - N inch	0.62
Dimension - Hole Size inch	0.56
Dimension - Length Overall inch	84.00 in
Dimensions	84 in x 3 in x 1 in

General

Plated	Y
Material - Ferrules	Y
Physical Attribute - Number of Braids	8
UPC	781810450062
Material	Copper
UPC 12 Digit	781810450062
UPC 14 Digit GTIN	00781810450062

Logistics

Minimum Pack Quantity	1
Pallet Quantity	90
Carton Quantity	1

Product Assets

[Catalog \[English\]](#)