



B2D10 Flexible Copper Braid

By Burndy
Catalog # B2D10

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
----------------	-------

Dimensions

Dimension - Pad Width inch	3
Package Height	0.000 in
Length	10 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	254 mm
Dimension - D inch	3
Dimension - N inch	0.62
Dimension - Hole Size inch	0.56
Dimension - Length Overall inch	10.00 in

General

Plated	N
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
UPC	781810116517
Material	Copper
UPC 12 Digit	781810116517
UPC 14 Digit GTIN	00781810116517

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3360
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)