



B2D14N Flexible Copper Braid

By Burndy
Catalog # B2D14N

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	CM
Status	
Industry Standard(s)	UL467

Configuration

Connector Type	Braid
----------------	-------

Dimensions

Dimension - Pad Width inch	0.94
Length	14 in
Dimension - L Length Overall mm	356
Dimension - D inch	3
Dimension - N inch	0.62
Dimension - Hole Size inch	0.56

General

UPC	781810454664
Material	Copper
UPC 12 Digit	781810454664
UPC 14 Digit GTIN	00781810454664

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1800
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)