



B2D36TNG89 Flexible Copper Braid

By Burndy
Catalog # B2D36TNG89

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

Specifications

Certification - CSA Approved	Yes
UL Listed	Yes
Standards - RoHS Compliance Status	CM

Current

Rating - Indoor Amperage	380
Rating - Outdoor Amperage	455

Dimensions

Dimension - Width inch	1.25
Dimension - Width mm	32 mm
Dimension - L Length Overall mm	914
Dimension - Length Overall inch	36
Length	36 in

General

Material - Ferrules	Copper
UPC	621945467064

Logistics

Minimum Pack Quantity	5
Carton Quantity	10
Pallet Quantity	900

Product Assets

[Catalog \[English\]](#)