



B2D7 Flexible Copper Braid

By Burndy
Catalog # B2D7

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

Specifications

Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	EX
Status	
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
----------------	-------

Current

Rating - Indoor Amperage	380
Rating - Outdoor Amperage	455

Dimensions

Dimension - Pad Width inch	0.94
Package Height	0.000 in
Length	7 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	178 mm
Dimension - D inch	2.50
Dimension - N inch	0.62
Dimension - Length Overall inch	7.00 in

General

Plated	N
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
UPC	781810201442
Material	Copper
UPC 12 Digit	781810201442
UPC 14 Digit GTIN	00781810201442

Logistics

Minimum Pack Quantity	1
Pallet Quantity	6000
Carton Quantity	75

Product Assets

[Catalog \[English\]](#)