



B2E10NSV Flexible Copper Braid

By Burndy
Catalog # B2E10NSV

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](http://www.hubbell.com/config/BRAID) for our Braid Configurator Tool:

Specifications

Certification - CSA Approved	No
UL Listed	Yes
Certification - ETL	No
Standards - RoHS Compliance	EX
Status	

Current

Rating - Indoor Amperage	530
Rating - Outdoor Amperage	635

Dimensions

Dimension - Pad Width inch	1.62
Dimension - D inch	3.12
Length	10 in
Dimension - N inch	0.62

General

UPC	781810092279
Plated	Y

Logistics

Minimum Pack Quantity	25
Carton Quantity	10
Pallet Quantity	1

Product Assets

[Catalog \[English\]](#)