



B2E15G127TN Flexible tinned copper braid 15.00"x1.62"x0.25"

By Burndy
Catalog # [B2E15G127TN](#)

Flexible tinned copper braid 15.00"x1.62"x0.25"



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](http://www.hubbell.com/config/BRAID) for our Braid Configurator Tool:

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Current

Rating - Indoor Amperage	530 A
Rating - Outdoor Amperage	635 A

Dimensions

Package Height	0.000 in
Length	15 in
Package Weight	0.000 lb.
Dimension - Width mm	41 mm
Dimension - Width inch	1.62
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	381
Height	0.25 in
Width	1.62 in
Dimension - Length Overall inch	15.00
Dimensions	15 in x 1.62 in x 0.25 in

General

Material - Ferrules	Tin Plated Copper
Physical Attribute - Number of Braids	2
UPC	781810543689
Material	Copper
UPC 12 Digit	781810543689
UPC 14 Digit GTIN	00781810543689

Logistics

Minimum Pack Quantity	1
Pallet Quantity	960
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)



A Hubbell brand