



B2E17N Flexible Copper Braid

By Burndy
Catalog # B2E17N

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](http://www.hubbell.com/config/BRAID) for our Braid Configurator Tool:

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	Yes
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Current

Rating - Indoor Amperage	530
Rating - Outdoor Amperage	635

Dimensions

Dimension - Pad Width inch	1.62
Package Height	0.000 in
Length	17 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	432
Dimension - D inch	3.00
Dimension - N inch	0.62
Dimension - Length Overall inch	17.00

General

UPC	781810649145
Material	Copper
UPC 12 Digit	781810649145
UPC 14 Digit GTIN	00781810649145

Logistics

Minimum Pack Quantity	1
Pallet Quantity	360
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)