



# B2E24N Flexible Copper Braid

By Burndy  
Catalog # B2E24N

Flexible Copper Braid



## Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: [www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

## Specifications

|                                    |       |
|------------------------------------|-------|
| Certification - ETL                | No    |
| Certification - UL Recognized      | No    |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | EX    |
| Certification - cULus              | No    |
| Industry Standard(s)               | UL467 |
| UL Listed                          | No    |
| Certification - CSA Approved       | No    |

## Configuration

|                |       |
|----------------|-------|
| Connector Type | Braid |
|----------------|-------|

## Current

|                           |     |
|---------------------------|-----|
| Rating - Indoor Amperage  | 530 |
| Rating - Outdoor Amperage | 635 |

## Dimensions

|                                 |           |
|---------------------------------|-----------|
| Dimension - Pad Width inch      | 1.62      |
| Package Height                  | 0.000 in  |
| Length                          | 24 in     |
| Package Weight                  | 0.000 lb. |
| Package Length                  | 0.000 in  |
| Package Width                   | 0.000 in  |
| Dimension - L Length Overall mm | 610 mm    |
| Dimension - D inch              | 3.00      |
| Dimension - N inch              | 0.62      |
| Dimension - Length Overall inch | 24.00 in  |

## General

|                                       |                |
|---------------------------------------|----------------|
| Plated                                | N              |
| Material - Ferrules                   | Y              |
| Physical Attribute - Number of Braids | 2              |
| UPC                                   | 781810077986   |
| Material                              | Copper         |
| UPC 12 Digit                          | 781810077986   |
| UPC 14 Digit GTIN                     | 00781810077986 |

## Logistics

|                 |      |
|-----------------|------|
| Pallet Quantity | 3600 |
| Carton Quantity | 25   |

## Product Assets

[Catalog \[English\]](#)