



# B2E26 Flexible Copper Braid

By Burndy  
Catalog # [B2E26](#)

Flexible Copper Braid.



## Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

## General

|                                       |                |
|---------------------------------------|----------------|
| Catalog Number                        | B2E26          |
| Connector Type                        | Braid          |
| Material                              | Copper         |
| Material - Ferrules                   | Y              |
| Physical Attribute - Number of Braids | 2              |
| Plated                                | N              |
| UPC                                   | 781810202487   |
| UPC 14 Digit GTIN                     | 00781810202487 |

## Dimensions

|                                 |        |
|---------------------------------|--------|
| Dimension - D inch              | 3      |
| Dimension - L Length Overall mm | 660 mm |

|                                 |          |
|---------------------------------|----------|
| Dimension - Length Overall inch | 26.00 in |
| Dimension - N inch              | 0.75     |
| Dimension - Pad Width inch      | 1.62     |
| Length                          | 26 in    |

## Electrical Ratings

|                           |     |
|---------------------------|-----|
| Rating - Indoor Amperage  | 530 |
| Rating - Outdoor Amperage | 635 |

## Certifications And Compliance

|                                    |       |
|------------------------------------|-------|
| Certification - ETL                | No    |
| Certification - UL Recognized      | No    |
| Certification - cULus              | No    |
| Industry Standard(s)               | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance        | EX    |
| Status                             |       |
| UL Listed                          | No    |

## Logistics

|                       |     |
|-----------------------|-----|
| Carton Quantity       | 2   |
| Minimum Pack Quantity | 1   |
| Pallet Quantity       | 180 |

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 30015682](#)  
[Specifications - B2E26](#)



A Hubbell brand