



B2E30N Flexible Copper Braid

By Burndy
Catalog # B2E30N

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](http://www.hubbell.com/config/BRAID) for our Braid Configurator Tool:

Specifications

Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	EX
Status	
Industry Standard(s)	UL467
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
----------------	-------

Current

Rating - Indoor Amperage	530
Rating - Outdoor Amperage	635

Dimensions

Dimension - Pad Width inch	1.62
Length	30 in
Dimension - L Length Overall mm	762 mm
Dimension - D inch	3.00
Dimension - N inch	0.62
Dimension - Length Overall inch	30.00 in

General

Plated	Y
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
UPC	781810276884
Material	Copper
UPC 12 Digit	781810276884
UPC 14 Digit GTIN	00781810276884

Logistics

Minimum Pack Quantity	1
Pallet Quantity	375
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)