



BURNDY

B2E72T58 Flexible Copper Braid

By Burndy
Catalog # [B2E72T58](#)
Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

Specifications

Certification - ETL

No
Certification - UL Recognized
No
Standards - Industry Standards Met
UL467
Standards - RoHS Compliance Status
EX
Certification - cULus
No
Industry Standard(s)
UL467
UL Listed
No
Certification - CSA Approved
No

Configuration

Connector Type
Braid

Dimensions

Length
72 in
Dimension - L Length Overall mm
1829 mm
Dimension - Hole Size inch
0.44 in
Dimension - Length Overall inch
72.00 in
Thickness - Pad
0.25 in

General

Plated
N
Material - Ferrules
Y
Physical Attribute - Number of Braids
2
UPC
781810200667
Material
Copper
UPC 12 Digit
781810200667
UPC 14 Digit GTIN
00781810200667

Logistics

Minimum Pack Quantity
1
Pallet Quantity
1
Carton Quantity
1

Product Assets

[Catalog.\[English\]](#)



A Hubbell brand
© 2026 Hubbell Incorporated. All rights reserved
BRDY-B2E72T58-SPEC-EN | REV 5/2026