



B2F106 Flexible Copper Braid

By Burndy
Catalog # B2F106

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](http://www.hubbell.com/config/BRAID) for our Braid Configurator Tool:

Specifications

Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	CM
Status	
Industry Standard(s)	UL467

Configuration

Connector Type	Braid
----------------	-------

Current

Rating - Indoor Amperage	600 A
Rating - Outdoor Amperage	720 A

Dimensions

Length	106 in
Dimension - L Length Overall	2692 mm
Dimension - Hole Size	0.56 inch
Dimension - Length Overall	106 inch
Thickness - Pad	0.38 in

General

Material - Ferrules	Copper
Physical Attribute - Number of Braids	2
UPC	781810466162
Material	Copper
UPC 14 Digit GTIN	00781810466162

Logistics

Minimum Pack Quantity	1
Pallet Quantity	900
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)