

B2F12N Flexible Copper Braid

By Burndy
Catalog # [B2F12N](#)

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Current

Rating - Indoor Amperage	600
Rating - Outdoor Amperage	720

Dimensions

Dimension - Pad Width inch	1.38 in
Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	305 mm
Dimension - Hole Size inch	0.56 in
Length	12 in
Dimension - D inch	3.00 in
Dimension - N inch	0.62 in
Dimension - Length Overall inch	12.00 in

General

Material - Ferrules	Y
Plated	N
Physical Attribute - Number of Braids	2
UPC	781810809129
Material	Copper
UPC 14 Digit GTIN	00781810809129

Logistics

Minimum Pack Quantity	1
Pallet Quantity	840
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)