



B2F20N Flexible Copper Braid

By Burndy
Catalog # B2F20N

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
Certification - cULus	No
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	No

Configuration

Connector Type	Braid
Current	
Rating - Indoor Amperage	600
Rating - Outdoor Amperage	720
Dimensions	
Length	20 in
Dimension - L Length Overall	508 mm
Dimension - Length Overall	20.00 in
General	
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
UPC	781810111703
Material	Copper
UPC 14 Digit GTIN	00781810111703

Logistics

Minimum Pack Quantity	1
Pallet Quantity	640
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)