



B2F26NX90TN Flexible Copper Braid

By Burndy

Catalog # [B2F26NX90TN](#)

Tin Plated Ferrules.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	B2F26NX90TN
Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
Plated	Y
UPC	781810200193
UPC 14 Digit GTIN	00781810200193

Dimensions

Dimension - Hole Size inch	0.54 in
Dimension - L Length Overall mm	660 mm
Dimension - Length Overall inch	26.00 in
Length	26 in
Thickness - Pad	0.38 in

Certifications And Compliance

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Carton Quantity	8
Minimum Pack Quantity	1
Pallet Quantity	320

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50115830](#)
[Specifications - B2F26NX90TN](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BRDY-B2F26NX90TN-SPEC-EN | REV 7/2025