



B2F32NTN Flexible Copper Braid

By Burndy
Catalog # B2F32NTN

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](http://www.hubbell.com/config/BRAID) for our Braid Configurator Tool:

Specifications

Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	EX
Status	
Industry Standard(s)	UL467

Configuration

Connector Type	Braid
----------------	-------

Current

Rating - Indoor Amperage	600
Rating - Outdoor Amperage	720

Dimensions

Length	32 in
Dimension - L Length Overall	813 mm
mm	
Dimension - Length Overall	32.00 in
inch	

General

Plated	Y
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
UPC	781810446393
Material	Copper
UPC 14 Digit GTIN	00781810446393

Logistics

Minimum Pack Quantity	1
Pallet Quantity	900
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)