



B2F84T38 Flexible Copper Braid

By Burndy
Catalog # [B2F84T38](#)

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:

www.hubbell.com/config/BRAID

Specifications

Certification - CSA Approved	Yes
UL Listed	Yes
Standards - RoHS Compliance Status	CM

Configuration

Connector Type	Braid
Dimensions	
Dimension - L Length Overall mm	2134
Dimension - Length Overall inch	84
Length	84 in
General	
Material - Ferrules	Copper
Physical Attribute - Number of Braids	2
Material UPC	Copper 621945469174
Logistics	
Minimum Pack Quantity	1
Carton Quantity	1
Pallet Quantity	96

Product Assets

[Catalog \[English\]](#)