



B2G10D75G150SV Flexible Copper Braid

By Burndy
Catalog # [B2G10D75G150SV](#)

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Certification - CSA Approved	Yes
UL Listed	Yes
Standards - RoHS Compliance Status	CM

Configuration

Connector Type	Braid
Dimensions	
Dimension - L Length Overall mm	273
Dimension - Length Overall inch	10.75
Length	10.75 in
General	
Material - Ferrules	Silver Plated Copper Ferrule
Physical Attribute - Number of Braids	2
Material	Copper
UPC	621945466395
Plated	Y
Logistics	
Minimum Pack Quantity	10
Carton Quantity	10
Pallet Quantity	900

Product Assets

[Catalog \[English\]](#)