



B2G10G146SV Flexible Copper Braid

By Burndy
Catalog # [B2G10G146SV](#)

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	CM
Status	
Industry Standard(s)	UL467
UL Listed	Yes
Certification - CSA Approved	Yes

Configuration

Connector Type	Braid
Dimensions	
Length	10 in
Dimension - L Length Overall	254 mm
Weight	2.95 lb.
Dimension - Length Overall	10 inch
General	
Plated	Y
Material - Ferrules	Silver Plated Copper Ferrule
Physical Attribute - Number of Braids	2
UPC	621945447912
Material	Copper
UPC 14 Digit GTIN	00621945447912
Logistics	
Minimum Pack Quantity	10
Pallet Quantity	900
Carton Quantity	10
Product Assets	
Catalog [English]	