



B2G11D50G129SV Flexible Copper Braid

By Burndy
Catalog # B2G11D50G129SV

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

Specifications

Certification - CSA Approved	Yes
UL Listed	Yes

Standards - RoHS Compliance CM
Status

Dimensions

Width	1.5 in
Weight	3.273 lb.
Height	0.5 in
Length	11.5 in
Dimensions	11.5 in x 1.5 in x 0.5 in

General

UPC	621945451933
-----	--------------

Logistics

Minimum Pack Quantity	1
Carton Quantity	5
Pallet Quantity	450

Product Assets

[Catalog \[English\]](#)