



B2G30D81TNCG1 Flexible Copper Braid

By Burndy
Catalog # B2G30D81TNCG1

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](http://www.hubbell.com/config/BRAID) for our Braid Configurator Tool:

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	UL467
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Current

Rating - Outdoor Amperage	700
---------------------------	-----

Dimensions

Package Height	0.000 in
Length	30.81 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	222 mm
Weight	7.8 lb.
Dimension - Length Overall	8.75 inch

General

Plated	Y
Material - Ferrules	Tin Plated Copper
Physical Attribute - Number of Braids	2
UPC	781810420751
Material	Copper
UPC 12 Digit	781810420751
UPC 14 Digit GTIN	00781810420751

Logistics

Pallet Quantity	70
Carton Quantity	2

Product Assets

[Catalog \[English\]](#)