



B2G84T38 Flexible Copper Braid

By Burndy
Catalog # B2G84T38

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](http://www.hubbell.com/config/BRAID) for our Braid Configurator Tool:

Specifications

Certification - CSA Approved Yes

UL Listed	Yes
Standards - RoHS Compliance Status	CM

Dimensions

Dimension - L Length Overall mm	84
Length	84 in

General

UPC	621945469167
-----	--------------

Logistics

Minimum Pack Quantity	1
Carton Quantity	1
Pallet Quantity	35

Product Assets

[Catalog \[English\]](#)