



B32F32G20TN Flexible Copper Braid

By Burndy
Catalog # B32F32G20TN

Flexible Copper Braid



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

Specifications

Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No

Configuration

Connector Type	Braid
----------------	-------

Current

Amperage Rating	1500 A
-----------------	--------

Dimensions

Length	32 in
Dimension - L Length Overall	813 mm
Dimension - Length Overall	32 inch

General

Plated	Y
Material - Ferrules	Y
Physical Attribute - Number of Braids	6
UPC	621945454576
Material	Copper
UPC 14 Digit GTIN	00621945454576

Logistics

Minimum Pack Quantity	1
Pallet Quantity	150
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)